



Insole for medium-high arches that makes your JALAS shoes even more comfortable and safe.

jalas® NEUTRALIZER 8710M MEDIUM ARCH



[Learn more](#)

MAKES YOUR MEDIUM-HIGH ARCHES HAPPY

The insole for medium arches makes your JALAS shoes more comfortable and safer. Poron® XRD® material in the forefoot and heel absorbs up to 90% of impact energy, providing outstanding shock absorption. This reduces injury risk and increases comfort. The insole is anatomically designed, ESD approved, and fits all JALAS safety shoes. Available in 17 sizes. Remove the original insoles before use. The JALAS FootStopService (FSS) scanner helps you choose the best insoles for your feet.

CHARACTERISTICS • Perfect fit • Extra comfortable • Breathable • Excellent shock absorption	FUNCTIONS • Heel/arch support • Double shock absorption zones • Approved for use in all JALAS® protective shoes • ESD • Anatomically designed • Perforated front section • Medium height arch
--	--



PREVENTS RISK OF

Antistatic, strain injuries

SPECIFICATION

TYPE Insoles

COLLECTION Neutralizer

MATERIAL Textile, Soft E.V.A, Polyester based electro conductive thread, Control bar in TPU, Double shock absorption zones in PORON® XRD®

COLOUR Green, Black

COMPLIANCE
FEATURES



ESD



Shock absorbing



Anti-static properties

SIZE				ARTICLE NUMBER	EAN
EU	UK	US M	US W		
34-35	1½-2	2½-3½	3½-4	8710M-34-35	6408487439445
36-37	4-5	4-5	5-6	8710M-36-37	6408487439452
38-39	5-6	5½-6½	6½-7½	8710M-38-39	6408487439469
40-41	6½-7	7½-8	8½-9	8710M-40-41	6408487439476
42-43	8-9	9-9½	10-11	8710M-42-43	6408487439483
44-45	10-10½	10½-11	11½-12½	8710M-44-45	6408487439490
46-47	11-12	12-13	13-14	8710M-46-47	6408487439506
48-50	13-15	13½-15½	14½-16½	8710M-48-50	6408487439513
34	1½	2½	3½	8710M-34	6408487563720
35	2	3½	4	8710M-35	6408487563782
36	3	4	5	8710M-36	6408487563843
37	4	5	6	8710M-37	6408487563904
38	5	5½	6½	8710M-38	6408487563966
39	6	6½	7½	8710M-39	6408487564024
40	6½	7½	8½	8710M-40	6408487564086
41	7	8	9	8710M-41	6408487564147
42	8	9	10	8710M-42	6408487564208
43	9	9½	11	8710M-43	6408487564260
44	10	10½	11½	8710M-44	6408487564321
45	10½	11	12½	8710M-45	6408487564383
46	11	12	13	8710M-46	6408487564444
47	12	13	14	8710M-47	6408487564505
48	13	13½	14½	8710M-48	6408487564567
49	14	14½	15½	8710M-49	6408487564628
50	15	15½	16½	8710M-50	6408487564680

ejendals

Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com