

## Features

- Wheeled
- Height Adjustable
- Available in different sizes

## RS PRO Polyurethane Hoker

RS Stock No.: 0687580



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

**RS PRO Polyurethane Hoker** is a modern solution designed for demanding work environments where comfort, durability, and ease of maintenance are essential. Built with high-quality materials and ergonomic design, it offers reliable support for everyday use.

#### Product Features:

- ✓ **Sturdy five-star chrome-plated base** – provides excellent stability and withstands intensive use
- ✓ **Stain-resistant surface** – easy to clean and maintain, even in challenging conditions
- ✓ **Rubber-coated castors** – protect floor surfaces from scratches and wear
- ✓ **Soft, anti-slip polyurethane seat** – ensures comfort and allows precise height adjustment for personalized use

An excellent choice for production, workshop, and technical environments where robust design and everyday comfort are important. Suitable for industries such as general manufacturing, automotive, technical services, and maintenance.

#### General Specifications

|                              |                                            |
|------------------------------|--------------------------------------------|
| TOTAL HEIGHT (mm)            | 550-675                                    |
| TOTAL WIDTH (mm)             | 640                                        |
| WEIGHT (kg)                  | 6,7                                        |
| MAX LOAD CAPACITY (kg)       | 120 (up to 200 kg with a special gas lift) |
| HEIGHT ADJUSTMENT RANGE (mm) | 430-555mm                                  |
| SEAT DIMENSIONS (mm)         | 330 x 200                                  |
| BACKREST DIMENSIONS (mm)     | 110 x 220                                  |
| COLOUR                       | BLACK                                      |
| MATERIAL                     | POLYURETHANE                               |
| BASE MATERIAL                | CHROME-PLATED STEEL                        |
| CASTORS                      | RUBBER-COATED TO PREVENT SCRATCHING        |

## Similar Products

| Stock No. | Brand  | Product Name                                     |
|-----------|--------|--------------------------------------------------|
| 0687581   | RS PRO | PU Hoker chair, seat height adjustment 515-700mm |
| 0687582   | RS PRO | PU Hoker chair, seat height adjustment 560-810mm |
| 0687576   | RS PRO | PU Stool chair, seat height adjustment 430-555mm |
| 0687577   | RS PRO | PU Stool chair, seat height adjustment 510-695mm |
| 0687579   | RS PRO | PU Stool chair, seat height adjustment 560-810mm |
| 0687583   | RS PRO | Stool chair, seat height adjustment 455-575mm    |
| 0687585   | RS PRO | Stool chair, seat height adjustment 535-715mm    |
| 0687586   | RS PRO | Stool chair, seat height adjustment 585-835mm    |

## Accessories

| Stock No. | Brand  | Product Name                                                                               |
|-----------|--------|--------------------------------------------------------------------------------------------|
| 0687597   | RS PRO | INDUSTRIAL castor, grey rubber tyre, diameter 50mm (**brake option available on request**) |
| XXX-XXX   | RS PRO | INDUSTRIAL metal castor, diameter 50mm                                                     |
| 0687598   | RS PRO | INDUSTRIAL glides                                                                          |
| 0687599   | RS PRO | INDUSTRIAL footrest                                                                        |
| 0687600   | RS PRO | INDUSTRIAL PU armrests                                                                     |
| 0687602   | RS PRO | INDUSTRIAL armrests, black steel + antistatic PU cover                                     |
| 0687604   | RS PRO | ESD armrests with height adjustment, black steel + antistatic PU covers                    |