








TABLE OF PART NUMBERS		
PART No.	TRANSMISSION CLASS	FRONT SHELL MATEIAL
RJX8FA3V2LPEB	CAT3	TYPE A
RJX8FB3V2LPEB	CAT3	TYPE B
RJX8FC3V2LPEB	CAT3	TYPE B BLACK
RJX8FA5V2LPEB	CAT5	TYPE A
RJX8FB5V2LPEB	CAT5	TYPE B
RJX8FC5V2LPEB	CAT5	TYPE B BLACK
RJX8FA6V2LPEB	CAT6	TYPE A
RJX8FB6V2LPEB	CAT6	TYPE B
RJX8FC6V2LPEB	CAT6	TYPE B BLACK



PCB LAYOUT
2:1
CONNECTOR REAR VIEW

- RJ45 CONTACTS
- RJ45 SHELL GROUND CONTACT
- SHIELD BOX LEGS
- CONNECTOR LOCATION PINS
- LED (SMD) POSITION



PANEL CUT OUT
2:1


SPECIFICATIONS:

1. MATERIALS:

- PLASTIC INSERT & HOUSING: HIGH TEMPERATURE THERMOPLASTIC FLAMMABILITY RATING UL94V-0 DSM STANYL, 30% BLACK
- FRONT METAL SHELL: ZINC ALLOY ZAMAK 3, NICKEL PLATE (B TYPE) OR BLACK COATING (C TYPE)
- CONTACTS: PHOSPHORE BRONZE, 1.27 um GOLD PLATE ON MATING SURFACES, 1.27 um NICKEL MIN UNDERPLATE. 3.81 um MIN MATTE TIN ON CONTACT TAILS.
- LATCH LOCK AND SPRING: SPRING STEEL, NICKEL PLATE.

2. ELECTRICAL CHARACTERISTICS:

- RATED VOLTAGE: 125 VAC
- TYPICAL CONTACT RESISTANCE: 20 mOhm
- INSULATION RESISTANCE: >500 MOhm
- DIELECTRIC STRENGTH: 1000 VAC, 60 SECONDS
- TRANSMISSION SPECIFICATION/CLASS: COMPLIES WITH CAT5e 1000 BASE-T PER EIA-568-C.2
- PoE+ COMPLIES WITH 802.3at Type 2 (SEE PSE PINOUT ALTERNATIVE TABLE)
- CAT5e AND CAT6 SUPPORT POE TYPE 1 TO 4 AND IEC60603-7 COMPLIANT



UNLESS OTHERWISE SPECIFIED TOLERANCE TO BE	
LINEAR	ANGULAR
X ± 0.5	X' ± 1
X.X ± 0.1	X.X' ± 30'
X.X ± 0.05	X.X.X' ± 15'

BREAK ALL SHARP EDGES AND REMOVE ALL BURRS

DO NOT SCALE

DIMENSIONS IN MILLIMETRES

THIS DOCUMENT IS THE PROPERTY OF AMPHENOL AUSTRALIA PTY. LTD.
NO PART THEREOF MAY BE REPRODUCED AND USED
WITHOUT THE PRIOR WRITTEN CONSENT OF THE OWNER.

MATERIAL:
REFER TO COMPONENTS

DRN: J.W
CKD: P.M

DATE: 07/09/2023
DATE: 07/09/2023

APP'D: P.M
SCALE:

DATE: 07/09/2023
SIZE: **A3**

Amphenol

Amphenol Australia Pty.Ltd,
22 Industry Blvd, Carrum Downs VIC 3201

TITLE:
**XLNet CONNECTOR
RJ45 RECP, VERTICAL
LIGHT PIPE, SHIELDED**

PART No:
REFER TO TABLE

DRAWING No.
55011536-000

REV
1

SHEET
2/16