

Han 24B-HTE/HSE-M50



Image is for illustration purposes only. Please refer to product description.

Part number	19 30 024 0499
Specification	Han 24B-HTE/HSE-M50
HARTING eCatalogue	https://harting.com/19300240499

Identification

Category	Hoods / Housings
Series of hoods/housings	Han [®] B
Type of hood/housing	Hood
Type	High construction

Version

Size	24 B
Version	Top/side entry
Number of cable entries	2
Cable entry	1x M50 1x M50
Locking type	Double locking lever
Field of application	Standard hoods/housings for industrial connectors

Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65 IP66 IP67
Type rating acc. to UL 50 / UL 50E	4 4X 12



Pushing Performance
Since 1945

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R1 (HL 1-3) R7 (HL 1-3)

Specifications and approvals

Approvals	CE DNV GL
-----------	--------------

Commercial data

Packaging size	1
Net weight	290 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140164987
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466