

Datasheet

Art.No. 92.052.9658.1

Male connector GST18i5F S2 R V SW

Device connectors, snap-in panel mount, GST18i5, 5 pole, male, spring clamp connection, 250/400 V, 20 A, material thickness 0,5 - 1,5 mm, colour of coding: black



Art.No.	92.052.9658.1
EAN	4015573399754
Order unit	100 pieces

Approvals



Technical data

General

Rated current	20 A
Rated voltage	400 V
Pollution degree	2
Mechanical coding	Code 1
Rated impulse voltage	4 kV
Interlockable	Yes
Color of coding/ contact carrier	Black
Marking of poles	

Connection Data

Connection cross section solid	2.5 mm ²
Cross section solid 2	0.5 mm ²
Connection cross section stranded	1.5 mm ²
Cross section stranded 2	0.5 mm ²
Terminations per pole	2

Model

Model	male
Number of poles	5
Connection type	Tension clamp connection
Connecting thread metric	No thread
Angle of plug	Straight

Degree of protection (IP)	IP40
Remark to type of connection	Finely stranded con. req. Wieland cable end sleeve
Thickness of housings (electrical device) 2	0.5 mm
Thickness of housings (electrical device)	1.5 mm
Built-in component	Snap-in

Material

Housing material	Polyamide
Halogen free	Yes
Contact material	CuZn
Insulation components continuous temperature	100 °C
Surface finish	Tin-plated

Dimensions

Length	38 mm
Width	52.3 mm
Height	18.5 mm



Drawings

