



**Product number** 1154890020  
**EAN** 4007123650361

## DESCRIPTION

- Robust, break and impact resistant plastic casing.
- Suitable for robust wall mounting.
- With an ergonomic carrying handle for comfortable carrying.
- Pre-wired and ready for connection.
- Protective cover for fuses.
- With RCD circuit breaker 30 mA for extra safety.
- Earthed sockets 230 V with 3 phases.

## TECHNICAL DATA

<b>Max. current carrying capacity</b>	32 A	<b>CEE 400 V / 32 A / 3P+N+PE (5p) Steckdosen</b>	1
<b>Miniature circuit breaker</b>	5	<b>Earthed socket outlets</b>	4
<b>Residual current circuit breaker (RCCB)</b>	FI with IFN 0.03 A (standard)	<b>Plug system socket</b>	Type F (Protective contact)
<b>Rated current (FI)</b>	30 mA	<b>Supply/ connection option</b>	Attachment plug
<b>Number of poles (FI)</b>	4	<b>Plug system plug</b>	CEE 32 A 3P+N+E (5p) 400 V
<b>CEE 400 V / 16 A / 3P+N+PE (5p) Steckdosen</b>	1	<b>Degree of protection (IP)</b>	IP44

## PACKAGING, DIMENSIONS AND WEIGHTS

<b>Packaging</b>	Coloured sales box	<b>Dimension LxWxH (without packing)</b>	28 cm x 34.9 cm x 13 cm
<b>UP</b>	1	<b>Weight of product (including packaging)</b>	3.81 kg
<b>Weight of product (without packaging)</b>	3.46 kg	<b>Dimension LxWxH (incl. packing)</b>	38 cm x 29 cm x 14 cm