

Han-Power T multi Han Q4/2



Image is for illustration purposes only. Please refer to product description.

Part number	61 12 203 0007 00
Specification	Han-Power T multi Han Q4/2
HARTING eCatalogue	https://harting.com/6112203000700

Identification

Category	Energy distributors
Series of hoods/housings	Han-Power® T
Element	Energy distributor
Specification	With 5x Han® Q 4/2 in Han-Compact® Housings, bulkhead mounting

Version

Number of contacts	6
Number of signal contacts	2
Number of power contacts	4
PE contact	Yes

Technical characteristics

Rated current	17 A
Rated voltage conductor-earth	400 V
Rated voltage conductor-conductor	690 V
Rated impulse voltage	6 kV
Pollution degree	3
Rated current (signal)	2 A
Rated voltage (signal)	24 V
Rated impulse voltage (signal)	4 kV
Pollution degree (signal)	3
Rated voltage acc. to UL	600 V



Pushing Performance
Since 1945

Technical characteristics

Rated voltage acc. to UL (signal)	24 V
Rated voltage acc. to CSA	600 V
Rated voltage acc. to CSA (signal)	24 V
Insulation resistance	$>10^8 \Omega$
Limiting temperature	-40 ... +40 °C
Mating cycles	≥ 500
Degree of protection acc. to IEC 60529	IP65

Material properties

Material (contacts)	Copper alloy
Material (hood/housing)	Polyamide (PA)
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	NBR
Material (locking)	Polyamide (PA)
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
UL / CSA	UL 2237 PVVA.E318390 CSA-C22.2 No. 182.3 PVVA7.E318390
Approvals	CE

Commercial data

Packaging size	1
----------------	---



Pushing Performance
Since 1945

Commercial data

Net weight	1,000 g
Country of origin	Germany
European customs tariff number	85444290
GTIN	5713140190559
eCl@ss	27142409 Small distribution board
ETIM	EC000214
UNSPSC 24.0	39121303