

Datasheet

Expansion Inserts



- Use in drilled or moulded-in holes
- Install by simple press or hammer-in methods
- Available with flush head, or flange head

Stock No.	Material	Thread Size	Fixing Hole Diameter	Body Outside Diameter	Body Depth	Thickness of Material Minimum	Mounting Depth
278-534	Brass	M3	4 mm	4.22 mm	4.78mm	6.7 mm	Flush
278-540	Brass	M3.5	4.8 mm	5.06 mm	6.35mm	8.4 mm	Flush
278-556	Brass	M4	5.6 mm	5.64 mm	7.95mm	10.2 mm	Flush
278-562	Brass	M5	6.4 mm	6.65 mm	9.35mm	12.2 mm	Flush
278-578	Brass	M6	8 mm	8.26 mm	12.7mm	16 mm	Flush
278-584	Brass	M3	4 mm	4.22 mm	4.78mm	6.2 mm	Flush
278-590	Brass	M3.5	4.8 mm	5.06 mm	6.35mm	7.8 mm	Flush
278-607	Brass	M4	5.6 mm	5.64 mm	7.95mm	9.4 mm	Flush
278-613	Brass	M5	6.4 mm	6.65 mm	9.53mm	11.2 mm	Flush
278-629	Brass	M6	8 mm	8.26 mm	12.7mm	14.8 mm	Flush