



CPSU range

12VDC & 24VAC power supplies



The CPSU have been designed to provide a reliable and stable supply voltage while providing a simple user friendly unit to install. This is achieved by having colour coded cable to advise the polarity of the input and mounting lugs to allow the unit to be fixed in place.

- 3 versions available
 - 12VDC 1.0amp
 - 12VDC 0.5amp
 - 24VAC 1.0amp
- Rated at continuous supply
- Mounting lugs
- UK plug fitted
- Colour coded low voltage cable
- Automatic gain control
- Rugged and versatile design

Range of PSU models

- CPSU-12-1.0A(B)** 12VDC, 1.0A power supply
- CPSU-12-0.5A(B)** 12VDC, 0.5A power supply
- CPSU-24-1.0A(B)** 24VAC, 1.0A power supply

The GANZ CPSU range have been designed to provide reliable, stable power source in a demanding environment

Specifications	CPSU-12-1.0A(B)	CPSU-12-0.5A(B)	CPSU-24-1.0A(B)
Model number	CPSU-12-1.0A(B)	CPSU-12-0.5A(B)	CPSU-24-1.0A(B)
Voltage output	12VDC	12VDC	24VAC
Current output	1.0A continuous	0.5A continuous	1.0A continuous
Voltage input	220 - 240VAC	220 - 240VAC	220 - 240VAC
Dimensions (L x W x H)mm	180 x 130 x 90	130 x 110 x 70	130 x 110 x 70
Weight	1,300g	750g	750g
Environment	-10 to +50 degrees C 85% relative humidity no condensing		
Mounting holes	Yes	Yes	Yes
Connector fitted	2.1mm	2.1mm	2.1mm
Colour coded cable	Yes	Yes	Yes
Mains connector	UK 3 pin	UK 3 pin	UK 3 pin

