

Product data sheet

Specifications



PLUG-IN BRIDGE, 4POINTS FOR 2,5MM² TERMINAL BLOCKS, RED

NSYTRAL24

Main

Range	Lineryg
Product name	Lineryg TR
Product or component type	Plug-in bridge
Device short name	TRA
Accessory / separate part category	Connection accessory
Product compatibility	TRV screw terminal terminal block TRP push-in terminal block TRR spring terminal terminal block TRH IDC terminal block
Number of ways	4 ways

Complementary

Cable cross section	2.5 mm²
Number of connections	4 2 3
Number of measurement input	4 2 1 6 3
Quantity per set	Set of 50
Net weight	3.4 g
Colour	Red

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.5 cm
Package 1 Width	6 cm
Package 1 Length	15 cm
Package 1 Weight	3 g
Unit Type of Package 2	BAG
Number of Units in Package 2	50

Package 2 Height	2.5 cm
Package 2 Width	6 cm
Package 2 Length	15 cm
Package 2 Weight	168 g
Unit Type of Package 3	S01
Number of Units in Package 3	1250
Package 3 Height	15 cm
Package 3 Width	15 cm
Package 3 Length	40 cm
Package 3 Weight	4.386 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)