

### **FEATURES**

- Versatile and easy to fit
- Can be screwed into place and removed manually
- Hexagonal shaped versions can be tighted using a wrench
- Lock PCB securely into place
- Nylon insulation material reduces the risk of electrical short circuits and is also lightweight and durable.
- Versions with nickel plated brass threaded inserts for resistance to corrosion

# RS PRO Nylon Round Standoff Female/Female, 20mm, M4 x M4

RS Stock No.: 653-9469



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



**Product Description** 

From RS Pro a range of high-quality standoffs made from solid nylon or with metal threaded inserts and a nylon insulation material. These versatile standoffs are designed to mount and secure your PCB as well as elevating your PCB from other components such as the inside of a computer chassis or another PCB, similar to spacers. They are also ideal for improving airflow space around components when the equipment becomes hot. These stand-offs are available in a range of different heights and threads sizes to suit a wide range of applications.

#### **General Specifications**

Gender Type	Female/Female
Material	Nylon
Body Shape	Round
Finish	Plain
Application	Office machinery, Telecommunications equipment, Consumer electronics, Audio visual equipment

#### **Mechanical Specifications**


Body Length	20mm
Thread Size	M6 x M6
Thread Size A	M6
Thread Size B	M6
Outside Diameter	8mm

#### Approvals

Compliance/Certifications	EN61340

## Standoffs





TYPE 1

TYPE 2