Auto Feed Screwdriver LXT®

DFR750

18V • 45 – 75 mm • 4 000 min^{-1}

Quick screwdriving with auto-feed system

A cordless 18V LXT screwdriver for screw strips with a speed of 4 000 min^{-1} and a robust aluminium auto-feed system for 45 – 75 mm screws. A precise depth control switch and screw guide ensure accuracy and prevent slanted screw feeds.



LXT

Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Collated drywall screw	45 - 75 mm
No load speed	4000 min^{-1}
Sound Pressure Level (L_{pA})	76 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	2,1 - 3,2 kg
Product Dimensions (L x W x H):	464 x 80 x 238 mm
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Driving Shank	1/4 "
Vibration Level, Screwdriving Without Impact	≤ 2,5 m/s^2
Vibration Uncertainty (K Factor), Screwdriving Without Impact	1,5 m/s^2

User benefits

- Depth adjustment
- Reversing switch
- Dust protected construction.
- Screw guide minimizes screw strip tangling
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makitauk.com

Related products

Optional AC

141352-1
Plastic Carrying Case



194500-1
Extension handle 890 – 990 mm



450128-8
Battery cover, LXT®, 14,4 – 18V



P-67804
Screw Bit, PH2, 177 mm, Ø 5 mm, 3

Other

User manual

Parts drawing