

Actuator

45-
2631.29N0.000

Distribution by
Rs-online



<https://rs-online.eao.com/p/45-2631.29N0.000>

Your product:



45-2631.29N0.000

Actuator

FRONT

Front dimension:	Ø 40 mm
Front form:	Round
Front bezel colour:	Silver
Front bezel material:	Metal

MOUNTING

Design:	Raised
Mounting cut-out:	Ø 22.3 mm
Mounting type:	Panel mounting

OPERATING-/INDICATION PART

Lens colour:	White
Lens material:	Plastic
Lens illumination:	Illuminated
Lens shape:	Mushroom-head
Lens optics:	transparent

MECHANICAL CHARACTERISTIC

Switching action:	Momentary
Switching system:	Slow-make switching element
Mechanical lifetime:	10 Mil. cycles of operation
Operating frequency:	Max. 3 600/h

Weight: 0.08 kg

AMBIENT CONDITION

IP front protection: IP66, IP67, IP69K

Operating temperature: – 25 °C ... + 70 °C

Storage temperature: – 40 °C ... + 80 °C

Shock resistance: According to IEC 60068-2-27: Sinusoidal half-wave 50 g / 11 ms

Vibration resistance: According to IEC 60068-2-6: 20 ... 500 Hz: 5 g

Climate resistance: During operation according to IEC 60721: 3K6, 3C3, 3S2, 3M6

CERTIFICATE

REACH: REACH compliant

RoHS: RoHS compliant


OTHER

Short Description: Actuator, Ø 22.3 mm, Ø 40 mm, Mushroom-head, Illuminated, White, Plastic, transparent, Round, Silver, Metal, Momentary, IP66, IP67, IP69K


Housing colour: Silver

Housing material: Metal

Wiring diagrams:



Mounting cut-outs:



Dimension drawings:

