

# 7445 // SONIC STEP FIT

Low shoes  
PPE risk category II



Sporty design  
With dial fastener 711 // FIT SYSTEM  
Heel reinforcement made of robust microfibre



## 7445 // SONIC STEP FIT



<b>Shoe upper:</b>	Split leather, grey   Action Leather, black
<b>Outsole:</b>	EVA / nitrile, black / white
<b>Size(s):</b>	36-48
<b>Packaging unit:</b>	10 pair(s)
<b>Certification:</b>	EN ISO 20345

NITRAS SONIC STEP FIT, safety shoes, S3S FO HRO SC, durable split leather / Action Leather, grey / black, durable EVA / nitrile outsole, black / white (colour code: 1210), fibreglass toe cap, textile perforation resistant midsole, metal-free, premium COMFORT STEP insoles, ergonomically formed, sporty design, with dial fastener 712 // FIT SYSTEM for fast availability and optimal fit, highest slip resistance (SR), width 11, heel lining for easy donning and doffing and heel reinforcement made of robust microfibre, DGUV Rule 112-191-protected, Type 1, ESD-capable, PPE risk category II

EN ISO 20345

EN IEC 61340-4-3



### Industries

-  Craft
-  Building / Construction
-  Landscape gardening
-  Waste management
-  Transport / Logistics

### Advantages

- + Sporty design
- + With dial fastener 711 // FIT SYSTEM
- + Heel reinforcement made of robust microfibre



Further images

---



**Additional information**

**Miscellaneous**

Weight (g) 560

**Logistics data**

Size	GTIN (SPU)	GTIN (PU)	Length (m)	Width (m)	Height (m)	Weight (kg)	Quantity PU / pallet
36	4059904209626	4059904209756	0,62 m	0,465 m	0,34 m	8,6 kg	
37	4059904209633	4059904209763	0,62 m	0,465 m	0,34 m	8,8 kg	
38	4059904209640	4059904209770	0,62 m	0,465 m	0,34 m	9 kg	
39	4059904209657	4059904209787	0,62 m	0,465 m	0,34 m	9,2 kg	
40	4059904209664	4059904209794	0,62 m	0,465 m	0,34 m	9,4 kg	
41	4059904209671	4059904209800	0,62 m	0,465 m	0,34 m	9,6 kg	
42	4059904209688	4059904209817	0,62 m	0,465 m	0,34 m	9,8 kg	
43	4059904209695	4059904209824	0,645 m	0,515 m	0,37 m	10 kg	
44	4059904209701	4059904209831	0,645 m	0,515 m	0,37 m	10,2 kg	
45	4059904209718	4059904209848	0,645 m	0,515 m	0,37 m	10,4 kg	
46	4059904209725	4059904209855	0,645 m	0,515 m	0,37 m	10,6 kg	
47	4059904209732	4059904209862	0,645 m	0,515 m	0,37 m	10,8 kg	
48	4059904209749	4059904209879	0,645 m	0,515 m	0,37 m	11 kg	

Customs tariff number: 64039993900

Country of origin: China