



S98MC1H

1/4" and 1/2" Square Drive Socket and Deep Socket Set with Metric Hex Profile, Hex Key Set and Combination Spanner Set - 98 pcs



PRODUCT DETAILS

- 11 hex sockets 1/4" standard 6700SM: 4.5, 5.5, 6, 7, 8, 9, 10, 11, 12, 13, 14 mm
- 10 hex deep sockets 1/4" A6800SM: 4, 5, 6, 7, 8, 9, 10, 11, 12, 13 mm
- 1 ratchet 1/4" quick release 6950QR
- 1 spinner handle 1/4" 6956
- 2 wobble extension bars 1/4" 6960W: 50 mm, 100 mm
- 1 T-handle 1/4" 6954-5
- 1 universal joint 1/4" 6966
- 1 bit holder 1/4" for 1/4" bits 6973A
- 17 hex sockets 1/2" standard 7800SM: 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 20, 21, 22, 24, 27, 30, 32 mm
- 1 ratchet 1/2" Quick Release 8150QR
- 2 wobble extensions 1/2" 8160W: 125 mm, 250 mm
- 1 T-handle adaptor 1/2" to 3/8" reductor 7772H
- 1 Universal joint 1/2" 8166
- 59/PH: 5 bits 1/4" PH0, PH1, PH2, PH3, PH4
- 59S/: 3 bits 1/4" flat: SL4, SL5.5, SL8
- 59/PZ: 3 bits 1/4" PZ1, PZ2, PZ3
- 59/H: 6 bits 1/4" Hex, H3, H4, H5, H6, H8, H10
- 59/T: 8 bits 1/4" Torx, T8, T10, T15, T20, T25, T27, T30, T40
- 1 hex male adaptor to square male adaptor K6625-1/4
- 9 pcs hex keys in set BE-9770: 1.5, 2, 2.5, 3, 4, 5, 6, 8, 10 mm
- 13 combination wrenches 111M: 7, 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19 mm
- Micro Matte finish
- High-performance 50BV30 alloy steel
- Less wear and damage to fastener thanks to Dynamic-Drive™ profile sockets
- Quick socket release button on ratchet
- Spare Case S98MC1H-BOX. High density polythene (HDPE)
- Standards: ISO 1174 and DIN 3120
- New Box Design
- Quick and Easy Action durable latches
- Soft touch Handle
- Hooks and shoulder strap for hands-free transportation
- Identification areas for sticker on the front and side

Follow the Fish!



PRODUCT ATTRIBUTES

Product				
S98MC1H	350 mm	350 mm	105 mm	6920 g

