

83/70 ROCK

A CEN6, LPCB SR3 approved High Security Padlock for securing the most valuable of sites and assets



SECURITY LEVEL



CERTIFICATIONS



CEN GRADE



TEST SEALS



The ABUS 83/70 is a CEN6 padlock and is built to secure assets of great value. It has a shackle and lock body manufactured from hardened special steel with a patented Nano Protect™ coating that makes it highly resistant to harsh conditions.

This padlock is designed to protect high security sites, assets and goods, largely in the critical national infrastructure markets.

The conventional design of this padlock means it has a wide range of applications such as gates, barriers, doors, containers and perimeter fencing.

The padlock is supplied to the end-user with an ABUS patented, registered, high security cylinder and key system.

Technology and features

- EN12320 CEN Grade 6
- Lock body and shackle made of hardened special steel
- Hardened special steel shackle with NANO PROTECT™ coating for very high corrosion protection
- Cylinder protected against drilling, bumping, pulling open
- Double bolted locking mechanism increases the security of the lock
- Cylinder protection cap against moisture and dust optionally available
- Shackle Type: Open

Width	70 mm
Height	128 mm
Thickness	30 mm
Shackle Diameter	15 mm
Vertical shackle clearance	38.5 mm
Horizontal shackle clearance	29.5 mm