

## Datasheet

# RS Pro Multi Function 8 Time Delay Relay, 01. s → 999 h, SPDT, 1 Contacts, 24 → 240 V ac/dc

RS Stock No: **896-6854**



## Product Details

RS Pro multi function 8 time delay relay has the option of 8 or 18 functions depending on the model. It is built-in a compact design for easy installation and has a digital display for easy viewing of run time and pre-set time. It has a time range of 0.1 s to 999 h with SPDT contact configuration. It has 1 contact and supply voltage of 24 to 240 V ac/dc.

## Features and Benefits

- Multifunction - 8 or 18 functions (depending on model)
- 17.5 mm wide
- 3-digit LCD display
- DIN rail mounting
- Wide operating voltage; 24 to 240 V ac/dc
- 0.1 s to 999 hours timing range
- Up/down counting modes
- Clear LED indication of relay status
- All settings programmed with only 2 keys
- Key lock function

**Specifications:**

Number of Timer Functions	8
Power Supply	External
Switch Configuration	SPDT
Time Increment	Hours, Minutes, Seconds
Depth	76 mm
Length	89 mm
Maximum Operating Temperature	+55°C
Minimum Operating Temperature	-10°C
Number of Contacts	1
Width	17.5 mm
Contact Configuration	1C/O
Current Maximum	8 A
Current Minimum	0.1 A
Maximum Voltage	240 V ac/dc
Minimum Voltage	24 V ac/dc
Mode of Operation	Multi Function
Mounting Type	DIN Rail
Supply Voltage	24 to 240 V ac/dc
Time Range	01. s to 999 h
IP Rating	IP20, IP40