



DBEE/U 1031 Multipole Receptacles

Contact polarity A

Contact polarity Z






Keying codes (View from F)

Code 1 (-1xx)

Code 2 (-2xx)

Code 3 (-3xx)




Solder (-x30/-x40)


PCB (-x39/-x49)

CONTACT CONFIGURATION	Contacts	Solder cup Ø	C	PIN Ø
1031 A Z 010	10	0.79	8.2	0.50
1031 A Z 012	12	0.79	8.2	0.50
1031 A Z 019	19	0.43	-	-

Pin layout / PCB hole pattern for polarity A - View from F (3)



Polarity Z - View from F



All dimensions in mm

Rev.

Pages

Notes :

- 1) All tolerances resulting from connector assembly are typically $\pm 0.3\text{mm}$
- 2) If receptacle is screwed directly into threaded hole, oversize thread by $+0.05\text{mm}$

3) Recommended PCB hole dimensions may be adjusted to application

4) Please contact us

Part number example : DBEE 1031 A019-130

600542

1

1/1

fischer
CONNECTORS

www.fischerconnectors.com