



PRODUCT DATASHEET

Datasheet creation date: 2025/05/28 10:49 (UTC)



23232CAME4

Spherical Roller Bearings

Parts Number

23232CAME4C3

Boundary Dimensions

d	160	mm	Bore diameter
D	290	mm	Outside diameter
B	104	mm	Width
r (min.)	3	mm	Chamfer dimension

Basic Load Ratings

Cr	1370000	N	Basic dynamic load rating
C0r	1770000	N	Basic static load rating

Speeds

Thermal Speed Rating (Oil-bath)	1500	min-1	Oil-bath lubrication subject to conditions outlined in ISO 15312
Mechanical (forced-circulation oil)	2200	min-1	Properly designed and controlled forced-circulation oil lubrication
Grease	1000	min-1	Grease lubrication
Oil (Oil-bath)	1300	min-1	Oil-bath lubrication

Abutment and Fillet Dimensions

da (min.)	174	mm	Diameter of shaft abutment
Da (min.)	245	mm	Diameter of housing abutment
Da (max.)	276	mm	Diameter of housing abutment
ra (max.)	2.5	mm	Radius of shaft or housing fillet

Calculation factors

e	0.34	Constant
Y2	2.9	Axial load Factors
Y3	2	Axial load Factors
Y0	1.9	Axial load Factors

Mass

Mass approx.	30.5	kg	Mass approx.
--------------	------	----	--------------

