

FEATURES

- **Sintered Bronze Material:** Provides excellent wear resistance and durability.
- **Flanged Design:** Facilitates easy installation and alignment.
- **Dynamic Load Rating of 14 N/mm²:** Ensures reliable performance under dynamic conditions.
- **Static Load Rating of 50 N/mm²:** Offers high load-bearing capacity for static applications.
- **Bore Size of 25.02 mm:** Suitable for a wide range of shafts.
- **Outside Diameter of 32.06 mm:** Fits standard housings.
- **Width of 30 mm:** Provides stability and support.

RS PRO 25.02 mm Plain Bearing, Flanged

RS Stock No: 558-474



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The RS PRO 25.02 mm Plain Bearing is a robust and reliable component designed for various industrial applications. Made from high-quality sintered bronze, this flanged bearing ensures smooth operation and longevity in demanding environments. Its primary benefit is reducing friction between moving parts, enhancing the efficiency and lifespan of machinery.

General Specifications

Bore Size	25.02 mm
Dynamic Load Rating	14 N/mm ²
Product Type	Plain Bearing
Static Load Rating	50 N/mm ²
Sub Type	Flanged

Mechanical Specifications

Material	Sintered Bronze
Outside Diameter	32.06 mm
Width	30 mm

Approvals

Standards/Approvals	ISO 2795, ISO 9001:2008, UKAS 001
---------------------	-----------------------------------

