

## FEATURES

- Voltage of 220 to 240 V ac
- Wattage of 200 W
- IP65 rated for protection against dirt and water
- One LED
- Luminosity of 1800 lm
- 4000 K colour temperature
- Dimensions of (W) 346 mm x (H) 470 mm x (D) 51 mm
- Life-span of around 30,000 hours
- Lamp supplied
- Beam angle of 115°
- Aluminium case

## RS PRO Floodlight, 200 W, 1800 lm, IP65 220 → 240 V ac

RS Stock No.: 188-3490



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Product Description

This RS PRO floodlight comes with a cool white LED (light-emitting diode) beam, capable of emitting 200 W (watts) and 18,000 lm (lumens). It's well-suited for a range of domestic and commercial jobs, from lighting-up a garage forecourt or warehouse exterior to brightening home exteriors. Part of the RS PRO range, the slim REX floodlight has been tested by engineers for both durability and consistency. It comes with a hardwearing but lightweight aluminium casing and an LED bulb that offers 30,000 hours of life.

### General Specifications

<b>Floodlight Type</b>	Outdoor
<b>Number of LEDs</b>	1
<b>Luminosity</b>	1800lm
<b>Light Colour</b>	Cool White
<b>Lumen Efficiency</b>	90lm/w
<b>Colour Index (CRI)</b>	Ra > 70
<b>Colour Temperature</b>	4000K
<b>PIR Included</b>	No
<b>Beam Angle</b>	115°
<b>Case Material</b>	Aluminium
<b>Housing Colour</b>	Black
<b>Applications</b>	Warehouses, Car Parks, Walkways, Construction areas, Parks and gardens, Home security

### Electrical Specifications

<b>Wattage</b>	200W
<b>Voltage</b>	220Vac to 240Vac
<b>Lamp Type</b>	LED
<b>Life Hours</b>	30000h
<b>Lamp Supplied</b>	Yes
<b>Lamp's Efficiency (%)</b>	>90 %
<b>Power Factor (PF)</b>	>0.9
<b>Dimmable</b>	No

**Mechanical Specifications**

<b>Dimensions</b>	346mm x 470mm x 51mm
<b>Height</b>	470mm
<b>Width</b>	346mm
<b>Depth</b>	51mm

**Protection Category**

<b>IP Rating</b>	IP65
------------------	------

**Approvals**

<b>Compliance/Certifications</b>	EN61340
----------------------------------	---------

