FlexSQUARE / LED Permanent Beacon 853 LED Perm. Beacon BWM 24VDC YE



Part No.: 853.300.55



MECHANICAL DATA 85 mm Length Width 85 mm Height 72 mm Materials PC PP-GF Dome colour Yellow Housing colour Black Protection category IP66 IP67 Connection Screw terminals cross-sectional area maximum 1,50mm² / 16AWG Cable entry Membrane grommet Cable entry minimum d = 1 mmd = 6 mm Cable entry maximum d = 12 mm d = 9 mm Type of fixing Base mounting Wall mounting -25°C Working temperature minimum +50°C Working temperature maximum Weight with packaging 166 g Product weight 132 g **ELECTRICAL DATA** 24V Operating voltage Operating voltage type DC Operating voltage tolerance +/- 10% Rated operational voltage 24 VDC Rated operational current 50 mA Rated inrush current 500 mA Protection class Protection class 2 Pollution degree 3 **OPTICAL DATA** Light source LED Light colour Yellow Optical signal image Permanent Service life optical 50,000 h maximum

APPROVAL DATA


For additional installation and mounting information, refer to the appropriate user guide at www.werma.com. This printed copy is for information only and is subject to alteration.

ļ

FlexSQUARE / LED Permanent Beacon 853 LED Perm. Beacon BWM 24VDC YE

Conforms with CE	Yes
WEEE	Yes
Conform with ATEX-directive	No
Conforms with CCC	No
Conforms with UL	No
Conforms with FCC	No
Conforms with IC	No
EAC certificate available	Yes
Conforms with AS-I	No
ICAO Certification	No
Conforms with DNV	No
Conforms with RoHS CN	No
Conforms with VdS	No

DRAWING



For additional installation and mounting information, refer to the appropriate user guide at www.werma.com. This printed copy is for information only and is subject to alteration.