


Go To Step Search™ Screen

280384-2 -- 1 of 1 products

AMPMODU

Through Hole Headers





Line art represents typical product only.

PCB Layout

Searchable Features:	
# of Rows	Dual
# of Positions	8
Breakaway Header	No
Profile	Standard
Shrouded	Yes
PCB Mount Angle	Vertical
PCB Retention Feature	Without
Surface Mount Compatible	No
Contact Mating Area Plating	Gold (15)
Board Standoff	Without
Mounting Ears	Without
Panel Attachment	No
Mating Connector Lock	With
Mating Connector Lock Type	Detent Windows
High Temperature Housing	No
Housing Style	3-Sided
Other Properties:	
Dim. A	.500 [12.70] in. [mm]
Dim. B	.300 [7.62] in. [mm]
Contact Material	Brass
Housing Material	Glass-filled Thermoplastic
Housing Flammability Rating	UL 94V-0
Housing Color	Black

[Main Menu | Help | Families | Registration | Feedback]

Top of Page