



24 mm 1/2" impact socket STD - 1pc

SHOCKWAVE™ IMPACT DUTY IMPACT SOCKETS

- SHOCKWAVE™ IMPACT DUTY steel (Chrome-Molybdenum) is high quality alloy steel which provides ultimate strength and durability.
- Best fitting thanks to 6 gripping points.
- Non-slip hex geometry to prevent socket and fastener rounding.
- Deep wall construction provides clearance for protruding bolts.
- Stamped and ink filled diameter markings and laser etched part number for wear resistance.
- Dual hole design and groove for security accessories.



Article Number	4932480318
For anchor thread size	M16
Outside diameter (mm)	34.2
Pack quantity	1
Size AF (across flats) (mm)	24
Tool reception	1/2" square
Total length (mm)	40
Working depth (mm)	13.9
Working length (mm)	13.9