

Rittal – The System.

Faster – better – everywhere.

► Slide rail, 1 U, depth- variable for VX IT, TE – IT 7063.750

Date : Apr 26, 2021

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Slide rail, 1 U, depth-variable for VX IT, TE – IT 7063.750

created: 26.04.2021 build on www.rittal.com/uk-en



Product description

Description: For direct attachment to the 482.6 mm (19") system punchings on the mounting angles. The slide rails are pulled out to the required length and secured between the front and rear mounting level on the 482.6 mm (19") pitch pattern.

Benefits: No loss of U
Thanks to the thin support surface of only around 0.8 mm thickness, exceeding the U pitch pattern is generally avoided, provided the components do not exceed a maximum height of 43.5 mm. In this way, several units may be easily arranged on top of one another without offset.

Applications: For mounting on the front mounting level

Material: Sheet steel

Surface finish: Zinc-plated

Supply includes: Assembly parts

Note: Effective contact surface 30 mm per side

Product description

To fit: Enclosure type: VX IT
Enclosure type: TS IT
Enclosure type: TE

Installation options: For attachment between the front and rear 482.6 mm (19") mounting level

Distance between levels: min.: 390 mm
max.: 550 mm

Contact surface:	Width: 30 mm
Units:	1 U
Load capacity:	20 kg static load
Packs of:	2 pc(s).
Weight/pack:	1.98 kg
Copper weight (kg per piece):	0
EAN:	4028177625440
Customs tariff number:	73269098
ETIM 7.0:	EC002625
ETIM 6.0:	EC002625
eCl@ss 8.0/8.1:	27189234
eCl@ss 6.0/6.1:	27182590
Product description:	DK Slide rail, Support surface Width: 30 mm, 1 U, depth-variable, 20 kg, static, distance between levels: 390-550 mm, For TS IT, TE
Approvals	
Certificates:	NA