

rotronic

Datenblatt - Fiche technique - Data sheet

11.04.5256




ROLINE VGA-Kabel HD15 ST – ST mit Ferritkern, 6,0m

ROLINE HD15 M/HD15 M avec noyaux de ferrite, 6,0m

ROLINE HQ VGA Cable with Ferrite, HD15 M – HD15 M, 6 m

CUSTOMER NO:	REMARK




NOTE:

- 1) PRIMARY DIM:A,C,D
- 2) FULLY COPPER FOIL SHIELD 360°.
- 3) CABLE AND MODEL COLOR:BLACK
- 4) RoHS COMPLIANT

13	NON UL PVC TUBE OD:2.3MM BLACK 6PCS RoHS
12	UL HEAT SHRINK TUBE BLACK OD:1.5mm RoHS 6PCS
11	UL HEAT SHRINK TUBE BLACK OD:3.0mm RoHS 6PCS
10	SOLDER WIRE RoHS
9	CABLE TIE BLACK 12cm RoHS
8	COPPER W:0.024M RoHS 2PCS
7	JUMP WIRE 24AWG 3CM RoHS
6	FERRITE CORE #17.5X28.5X#9.5mm RoHS
5	SCREW:#4-40UNC E:40.2MM BLACK(1101) RoHS
4	INNER JACKET PE RoHS
3	OUTER JACKET PVC 45Po BLACK(1101) RoHS
2	HDB15M BLUE SOLDER TYPE TERMINAL PLATED GOLD FLASH W/O 9PIN RoHS
1	UL2919 28#*3COAX+2B#7C+AL+MY+B(1/65%)+D BALCK(1101) OD:8.0MM LENGTH RoHS


PINOUT:



A	FIRST EDITION	He X.Lin	18/04/09
REV.	ECR	DESCRIPTION	C.N. DATE
<small>THIS DRAWING AND SPECIFICATIONS ARE THE PROPERTY OF ROTRONIC CO. UNLESS SHOWN OTHERWISE. NO PARTS MAY BE REPRODUCED OR TRANSMITTED IN ANY FORM OR BY ANY MEANS WITHOUT THE WRITTEN PERMISSION OF ROTRONIC CO. UNLESS SHOWN OTHERWISE.</small>		Rotronic Co., Ltd	
<small>PLEASE CONTACT SPECIFIC COMPANIES ARE IN ALLIANCE WITH ROTRONIC CO. UNLESS SHOWN OTHERWISE.</small>		MONITOR CABLE	
<small>DIMENSIONS</small> <small>0.01 TO 20.00mm</small> ±0.10mm <small>20.01 TO 80.00mm</small> ±0.12mm <small>80.01 TO 100.00mm</small> ±0.15mm <small>100.01mm</small> ±0.20mm	<small>TOLERANCES</small> <small>±0.10mm</small> <small>±0.12mm</small> <small>±0.15mm</small> <small>±0.20mm</small>	<small>DRG.</small> <small>CHK.</small> <small>APP.</small>	<small>DATE</small> <small>APP.</small>
<small>INTERNAL</small> <small>FINISH</small>	<small>PROJ. NO.</small> W28SBK1MMXX	<small>SCALE</small> <small>SHEET</small> 1/2	<small>REV.</small> A

CUSTOMER NO:	REMARK

客戶料號	長度(M)	包裝方式	紙箱尺寸			裝箱數量
			高(cm)	長(cm)	寬(cm)	
11.04.5252	2.0	吊卡+PE袋(8"×10"×0.08mm)	20	37	30	20
11.04.5253	3.0	吊卡+PE袋(8"×10"×0.08mm)	17	46	30	20
11.04.5256	6.0	吊卡+PE袋(8"×10"×0.08mm)	17	46	30	10
11.04.5260	10	PE袋(9"×14"×0.08mm)	20	32.5	25	5
11.04.5270	20	PE袋(12"×14"×0.08mm)	18	26	26	2
11.04.5280	30	PE袋(14"×16"×0.08mm)	18.5	36.5	30	2



- NOTE:
- 1)線材長度和PE BAG規格參表格.
 - 2)貼紙由業務提供.
 - 3)各長度的線材,紙箱尺寸和裝箱數量參上表格.
 - 4)產品符合RoHS標準.

A	FIRST EDITION	He X.Lin	18/04/09
REV. ECR	DESCRIPTION	C.N.	DATE
<small>THIS DRAWING AND SPECIFICATIONS ARE THE PROPERTY OF ROTRONIC CO. ANY REPRODUCTION OR USE WITHOUT THE WRITTEN CONSENT OF ROTRONIC CO. IS STRICTLY PROHIBITED.</small>		Rotronic Co., Ltd	
<small>UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS AND UNLESS OTHERWISE SPECIFIED TOLERANCES ARE:</small>		MONITOR CABLE	
DIMENSIONS	TOLERANCE	DRWD.	APP.
0.00 TO 25.00mm	±0.10mm		
25.01 TO 50.00mm	±0.15mm		
50.01 TO 100.00mm	±0.20mm		
100.01mm +	±0.25mm		
MATERIAL		REV.	
FINISH		W28SBK1MMXX	
		SHEET 2/2	UNIT MM
		SIZE A4	REV. A