

64210NBU

NIGHT BREAKER UNLIMITED | Halogen headlight lamps for cars



Areas of application

- Headlight

Product benefits

- Up to 110 % more light on the road (compared to standard halogen lamps)
- Up to 40 m longer beam of light (compared to standard halogen lamps)
- Up to 20 % whiter light (compared to standard halogen lamps)
- Drivers spot obstacles and dangerous situations much sooner
- Optimum light for more reaction time
- Patented blue ring coating for less reflected glare
- More efficient light production thanks to optimized inert filling gas formula
- Higher resilience due to robust coil design

Product features

- Eye-catching design with partial blue coating and silver cap

Product datasheet

Technical data

Electrical data

Power input	58 W ¹⁾
Nominal wattage	55.00 W
Nominal voltage	12 V
Test voltage	13.2 V

¹⁾ Maximum

Photometrical data

Color temperature	3600 K
Luminous flux	1500 lm
Luminous flux tolerance	±10 %

Dimensions & weight

Length	59.0 mm
Diameter	12.0 mm
Product weight	12.50 g

Lifespan

Lifespan B3	150 h
Lifespan Tc	250 h

Additional product data

Base (standard designation)	PX26d
-----------------------------	-------

Certificates & standards

ECE category	H7
--------------	----

Country specific categorizations

Order reference	64210NBU 55W 12
-----------------	-----------------

Country specific information

Product code	METEL-Code	SEG number	STK-Number	UK Org
4052899017061	-	8328015	-	-

Product datasheet

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (height x width x length)	Volume	Gross weight
4052899016972	64210NBU	Folding carton box 1	58 mm x 34 mm x 34 mm	0.07 dm ³	15.50 g
4052899016989	64210NBU	Bundle 10	58 mm x 69 mm x 170 mm	0.68 dm ³	156.00 g
4052899016996	64210NBU	Shipping carton box 100	129 mm x 186 mm x 356 mm	8.54 dm ³	1757.00 g
4052899017009	64210NBU	Unpacked 1	- x - x -		
4052899017016	64210NBU	Shipping carton box 180	240 mm x 255 mm x 345 mm	21.11 dm ³	2877.00 g
4052899017023	64210NBU	Blister 2	35 mm x 140 mm x 135 mm	0.66 dm ³	42.00 g
4052899017030	64210NBU	Shipping carton box 20	145 mm x 145 mm x 363 mm	7.63 dm ³	543.00 g
4052899017047	64210NBU	Blister 1	35 mm x 95 mm x 135 mm	0.45 dm ³	34.50 g
4052899017054	64210NBU	Shipping carton box 10	145 mm x 115 mm x 279 mm	4.65 dm ³	435.00 g
4052899017061	64210NBU	Hard Cover Box 2	47 mm x 93 mm x 111 mm	0.49 dm ³	111.00 g
4052899017078	64210NBU	Shipping carton box 20	106 mm x 240 mm x 250 mm	6.36 dm ³	1230.00 g
4052899017085	64210NBU	Hard Cover Box 2	95 mm x 47 mm x 115 mm	0.51 dm ³	109.00 g
4052899017092	64210NBU	Shipping carton box 20	106 mm x 240 mm x 250 mm	6.36 dm ³	1230.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.