

PRODUCT-DETAILS

216MVS6WH

Switched interlocked socket-outlet, vertical,
Heavy Duty, 6h, 16A, IP67, 2P+E



General Information

Extended Product Type	216MVS6WH
Product ID	2CMA163257R1000
EAN	7392696632577
Catalog Description	Switched interlocked socket-outlet, vertical, Heavy Duty, 6h, 16A, IP67, 2P+E
Long Description	Switched Interlocked Socket Outlet, vertical, Heavy Duty, earthing sleeve position 6h, rated current 16A, IP67 watertight, 2-poles+earth

Ordering

E-Number (Sweden)	E2417133
E-Number (Finland)	2417133
E-Number (Norway)	2417133
EAN	7392696632577
Country of Origin	Czech Republic (CZ)
Minimum Order Quantity	1 piece

Dimensions

Product Net Width	160 mm
Product Net Height	205 mm
Product Net Weight	1.83 kg
Mechanical Drawings	9AKK107991A3924

Container Information

Package Level 1 Width	215 mm
Package Level 1 Depth / Length	335 mm
Package Level 1 Height	165 mm
Package Level 1 Gross Weight	1.83 kg
Package Level 1 EAN	7392696632577
Package Level 1 Units	box 1 piece
Package Level 2 Width	800 mm
Package Level 2 Depth / Length	1200 mm
Package Level 2 Height	900 mm
Package Level 2 Gross Weight	96.86 kg
Package Level 2 EAN	7392696068277
Package Level 2 Units	pallet (lift) 42 piece

Environmental

RoHS Status	Following EU Directive 2011/65/EU
SCIP	Czech Republic - 8f2a459d-ae21-4edc-8431-c56a61d9e5ef

Certificates and Declarations (Document Number)

Declaration of Conformity - CE	2CMC700005D0001
Environmental Information	2CMC000057M0000
RoHS Information	2CMC700005D0001
SEMKO Certificate	2CHC660004X0203
REACH Declaration	2CMC700005D0001

Additional Information

Additional Information	2P+E
Ambient Temperature	-25 ... 40 °C
Cable Cross-Section	1.5 ... 4 mm ²
Cable Diameter	6 ... 13 mm
Cable Entry Position	Knock-out on Top and drill marks down
Cable Outlets Per Side	1xØ40+1xØ50 mm on top and drill marks on bottom
Color	Blue
Connection Type	Screw
Degree of Protection	IP67 IP69
Frequency (f)	50 Hz 60 Hz
Function	Switched Interlocked Socket outlet, vertical, Heavy Duty
Housing Material	Thermoplastic (PBT)
Invoice Description	IND. P&S#216MVS6WH
Mounting Holes	79.5x79.5
Mounting Type	Vertical
Number of Poles	3

Order Multiple	1 piece
Product Main Type	CMVS
Product Name	Industrial Switched Interlocked Socket Outlet
Protection Type	Switched Interlocked
Rated Current (I_n)	16 A
Rated Voltage (U_r)	200 ... 250 V
Recommended Screw Driver	PH2
Standards	IEC 60309-1, -2, -4
Suitable For	Switched Interlocked Socket Outlets, Vertical
Suitable for Product Class	IEC Industrial Plugs and Sockets
Instructions and Manuals	2CMC000029M0001
Installation Manual	2CMC000029M0001
RAL Number	RAL 7001 - Silver Grey

Classifications

eClass	27440510
UNSPSC	39120000

Technical

Wire Size	14 ... 12 AWG
Tightening Torque	WireClamp0.8 N·m

Categories

Low Voltage Products and Systems → Industrial Plugs and Sockets → Critical & Safe → Switched Interlocked Socket Outlets

