




P1: DVI (18+5)



L(mm)




#4-40 UNC(X4)



P2: HDB15M

PIN OUT



NOTES:

1. MATERIAL

1.1 HDMI CABLE: (7/0.12TC+FPE+30/0.10TC+FAM)\*3CO+7/0.12TC\*1P  
+7/0.12TC\*5C+AL+7/0.12TC+128/0.12ALM+BLACK PVC JACKET  
OD: 7.5 ± 0.2 mm

1.2 DVI-D (18+5) MALE: BLACK INSULATION, GOLD PLATED CONTACTS  
NICKET PLATED SHELL.

1.3 HIGH DENSITY D-SUB 15PIN MALE: BLACK INSULATION, GOLD PLATED  
CONTACTS, NICKET PLATED SHELL.

1.4 ALL HOOD: MOLDED BLACK PVC.

2. ELECTRICAL

2.1 100% OPEN AND SHORT TEST.

2.2 CONDUCTOR RESISTANCE: 5 OHMS MAX.

2.3 INSULATION RESISTANCE: 5 MEGOHMS MIN/DC300V.

2.4 HI-POT: DC200V/0.01S.

2.5 HDTV-DVD TEST : 1080P.

3. PACKAGING: BULK PACKAGING.

4. ALL COMPONENTS ARE RoHS AND REACH COMPLIANT.

P/N表

ITEM NO.	L
11.99.5449	5000 ± 70mm
11.99.5430	3000 ± 70mm
11.99.5420	2000 ± 50mm

DRAWING APPROVED _____		DATE: _____	
SAMPLE APPROVED PER DRAWING SPECIFICATIONS _____		DATE: _____	
	mm	TITLE VALUE DVI-VGA CABLE	
SCALE	NONE	CUS. NAME	
SHEET	1/1	CUS. P/N	
DIMENSIONAL TOLERANCES UNLESS OTHERWISE NOTED		DRAWING NO. HF0487	
.X ±	.XX ±	ENG.	DATE YICO 2011-3-22
.XX ±	ANGLES ±	CHECKED	DATE SALLY 2011-3-22
REV. 00	CUS. REV 00	APPROVED	DATE SUNNY 2011-3-22

REV.	MODIFY DESCRIPTION	DATE
00	NEW ISSUE	2011-3-22