

ENGLISH

Datasheet

Stock No: 285-8845

RS Pro 15mm Elbow Coupler Brass Compression Fitting





Product Details

Stop End (Compression End to Hexagon Headed Stop End) Note

See 'Key characteristics' table for guide to pressure/temperature.

Fittings - Chrome Plated Brass

Chromium plated brass fittings.

Type A fittings suitable for mechanically joining metric o/d tubing in accordance with: Copper tube to BS2871: Part 1: Table X Table Z. Stainless steel tube to BS4127: Part 2: 1972.

For suitable chromium plated copper tube

BS864/2 BSI Kitemark Licence no. KM07082



ENGLISH

| Key Characteristics | | | | |
|--|---------------------------|-----------------------|------|--|
| Medium | Service Temperature up to | Max. Working Pressure | | |
| | °C | BAR | PSI | |
| Water or light mineral oils 8 to 54mm sizes | 30 | 16 | 230 | |
| | 65 | 10 | 145 | |
| | 110 | 6 | 87 | |
| | 120 | 5 | 75 | |
| Compressed air non-shock 8 to 28mm sizes only | 30 | 7 | 100 | |
| Saturated steam | 120 | 3 | 4545 | |
| LPG & Natural Gas 8 to 28mm sizes only | 30 | 1 | 15 | |

Specifications:

| Compression Connection Pipe Diameter | 15mm |
|--------------------------------------|---------|
| Fitting Type | Coupler |
| Material | Brass |
| Fitting Direction | Elbow |