













REV	ECN NO.	DESCRIPTION	SIGN	DATE
A				



CUSTOMER APPROVED:		RACE MODEL:	
VISION DISPLAY SOLUTIONS		CUSTOMER MODEL: RTP-065	
SCALE	UNIT	DESIGNED	CQL
1:1	mm	CHECKED	LCB
REV	Ver.1	APPROVED	PGJ
	SIZE A3	SHEET	1 OF 1

Pin No.	Description	XL	YU	XR	YD
1					
2					
3					
4					



Please double check the points marked in finger.

- Notes:
- Type: Film to Glass
 - Operating Voltage: ≤5V
 - operation Temperature: -20°C~70°C
 - Storage Temperature: -30°C~80°C
 - Response Time: ≤10ms
 - Life Time: ≥1,000,000 times
 - Connect Material: FPC
 - Linearity: ≤1.5%
 - Transmittance: ≥78%
 - Surface Hardness: ≥3H (Pencil)
 - operation force: ≤120g
 - Resistance: (Anti-glare Hard & Mate anti-newton ring coating ITO Film) Y: 1500~5500 (Stand and ITO Glass) X: 3000~9000
 - Unspecified Tolerance: ±0.30
 - All materials in the drawing coincide with the RoHS & halogen free requirement