



# WD Elements™

Desktop HDD Storage

Product Specifications	Average latency	N/A	
	Average read seek	N/A	
	Battery	No	
	Cache/Buffer	N/A	
	Interface transfer rate	5 Gb/s (maximum)	
	Disk Capacity*	6TB	
	Drive Bays	N/A	
	Interfaces	N/A	
	Memory	N/A	
	Processor	N/A	
	Rotational Speed	N/A	
	Tape Drive	N/A	
	Write Speed	N/A	
Product Dimensions	Length	5.31 in	135.00 mm
	Width	1.89 in	48.00 mm
	Height	6.53 in	165.80 mm
Product Weight	6TB	2.09 lb	0.95 kg
Colors available		N/A	
Country Code / Origin		Product of Thailand	
Environmental Specifications	Operating Temperature	5° C to 35° C	
	Non-op Temperature	–20° C to 65° C	
	Operating relative humidity	N/A	
	Non-operating relative humidity	N/A	
Power Specifications	AC input voltage (AC adapter)	100 – 240V	
	AC input frequency	50 – 60 Hz	
Languages for software		N/A	
Languages for User Manual		N/A	
Licenses Included		N/A	
Limited Warranty***		2 years	
Previous Product Model	Product Name	N/A	
	Ref Order Number	N/A	
Regulatory	NRCAN compliant	N/A	
	RoHS compliant**	Yes	
Software included		N/A	

1TB = one trillion bytes. Actual user capacity may be less depending on operating environment.

\* 1 TB = one trillion bytes. Actual user capacity may be less depending on operating environment.