



Brand of NTN corporation

Technical data

UKP309H

Bearing units




Grey cast housing, radial insert ball bearing with adapter sleeve, seal with slinger

KIT CONTENT

UK309G2H, P309

VISUAL (S)



PRODUCT DEFINITION

Brand	SNR
A - Housing width	67 mm
A1 - Housing top width	45 mm
B - Width of Inner Ring	38 mm
d - Shaft diameter	40 mm
d1 - Outer dia of eccent. Lock. collar / nut of adapter sleeve	65 mm



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

PRODUCT DEFINITION

G - Grease fitting	M6x1
H - Distance mounting base to centerline spheric. seating diam.	67 mm
H1 - Housing foot height	24 mm
H2 - Housing height	129 mm
J - Mounting holes distance	190 mm
L - Housing length	245 mm
L1 - Housing foot length	65 mm
N - Mounting hole dimension	20 mm
N1 - Mounting hole length	30 mm
s1 - Distance nut to middle of bearing raceway	30 mm

PRODUCT PERFORMANCE

C - Dynamic load rating	53000000 mN
C0 - Static load rating	31800000 mN
Operating temperature min.	253,15 °K
Operating temperature max.	373,15 °K

OTHER FEATURES

Mass	4,64 kg
Adapter sleeve designation	H2309

