

## Art. no. TVVR11002

Page 1 of 2



The watertight protective housing (up to 20m) and wide mount equipment enable versatile application – be it as hand camera or on a surfboard, a mountain bike, when paragliding or on a motocross tour. With the mounts and housing included in the price this Sportscam is the all-rounder for everyone. Furthermore, the camera can be controlled via remote control (included). Thus hands stay free and pauses for operating the device are not needed.

# Sportscam Full HD Set

Art. no. TVVR11002

Page 2 of 2

**Technical Data:**

Dimensions	(HxWxD) 85 x 50 x 23 mm
Connections	Mini USB, mini HDMI, AV out
Audio	Installed microphone
Recording resolution @ frame rate per camera	1080p, 960p, 720p, WVGA @ 30 fps, 720p @ 60 fps
Recording modes	Permanent, noise detection (from 65 dB)
Recording duration	0,2 hours/GB
Battery operation	3 hours at permanent recording
Operating mode	Simplex
Image sensor	CMOS
Pixels (effective)	1920 x 1080 pixel
Pixels (total)	2000 x 1241 pixel
Width	50 mm
Gross weight	0.825 kg
Height	85 mm
Horizontal angle of view	128° (1080p, 960p), 170° (720p, WVGA) °
Camera outputs	AV, mini HDMI

Camera type	Colour camera
Length	23 mm
Max. operating temperature	60 °C
Max. humidity	85 %
Microphone	yes
Min. operating temperature	-10 °C
Monitor	1.5 "
Net weight	0.081 kg
DC voltage supply	3.7 V
Storage medium	Micro SD card
Power consumption	350 mA
Video compression	H.264
Certifications	CE