

PRODUCT-DETAILS

# TY26M-7

## CABLE TIE 40LB 11IN PURPLE NYLON



### General Information

Extended Product Type	TY26M-7
Product ID	7TAG009000R0235
EAN	5414363062851
Catalog Description	CABLE TIE 40LB 11IN PURPLE NYLON
Long Description	Cable Tie, Purple Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21 Rated for AH-2 Plenum, Length of 277mm (10.9 Inches), Width of 3.6mm (0.14 Inches), Thickness of 1mm (0.04 Inch), Tensile Strength Rating of 134 Newtons (30 Pounds), Bulk Pack

### Ordering

EAN	5414363062851
UPC	786210659435

### Dimensions

Product Net Width	0.14 in 3.6 mm
Product Net Depth / Length	10.9 in 277 mm

### Container Information

Package Level 1 Units	1000 piece
-----------------------	------------

Package Level 1 Width	6.8 in 173 mm
Package Level 1 Height	5.1 in 130 mm
Package Level 1 Depth / Length	12.3 in 312 mm
Package Level 2 Units	10000 piece
Package Level 2 Width	9.6 in 244 mm
Package Level 2 Height	13.7 in 348 mm
Package Level 2 Depth / Length	21.3 in 541 mm

---

## Technical UL/CSA

Flammability According to UL94	V-2
--------------------------------	-----

---

## Additional Information

Effective Date	19961210
Number of Batteries	0
Product Name	NYLON CABLE TIES AND ACCESSORIES

---

## Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TDS000566
Declaration of Conformity - CE	9AKK107492A9841
Instructions and Manuals	TY26M-7

---

## Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

---

## Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

