

USB C Multiport Adapter - USB-C to HDMI 2.0b 4K 60Hz (HDR10), 100W Power Delivery Pass-Through, 4-Port USB 3.0 Hub - USB Type-C Mini Dock - 12" (30cm) Long Attached Cable

**Product ID:** DKT30CHPD3



This USB-C multiport adapter with DP 1.4 supports 4K 60Hz HDMI and turns your MacBook Pro, Dell XPS, or other USB-C laptops or tablet into a workstation, anywhere you go. The USB Type-C multiport adapter provides 4K HDMI video output, three USB 3.2 Gen 1 Type-A (5Gbps) ports including one BC 1.2 charge port; one USB-C port supporting both the 100W PD passthrough, all through one connection to your laptop's USB-C or Thunderbolt 3 port. Plus, it offers advanced charging through USB Power Delivery 3.0 and an extra-long attached 12-inch (30 cm) host cable for an extended reach to offer more set up flexibility.

The portable docking station connects your laptop to a 4K 60Hz HDMI monitor (4096 x 2160p) to create a powerful workstation. It can also connect to an ultrawide monitor.

The USB-C to USB 3.1 Gen 1 hub gives you three USB-A ports to connect your legacy USB devices, plus one shared USB-C port for either power delivery pass through.

With support for USB PD 3.0 (up to 100W), the USB Type-C multiport adapter lets you power and charge your laptop, and power your peripherals when connected to a USB-C power adapter. PD 3.0 features Fast Role Swap to prevent USB data disruption when you switch power sources (USB-C power adapter to bus power).

The DKT30CHPD3 is backed by a StarTech.com 3-year warranty and free lifetime technical support.

Note: To ensure full adapter functionality, your laptop's USB-C port must support USB Power Delivery.

## Certifications, Reports and Compatibility

## Applications

## Features

- **5-IN-1 MULTIPORT ADAPTER:** USB-C multiport adapter with DP 1.4 Alt-Mode up to 4K 60Hz (4K 30Hz with DP 1.2) HDMI 2.0b (HDR10) video; 4-Port USB Hub 5Gbps: 3x USB-A (USB 3.2/3.1 Gen 1) with 1x BC 1.2 charging, 1x USB-C (100W PD Passthrough)
- **EXTRA LONG CABLE:** USB C to HDMI multiport adapter with 12" (30cm) attached cable for extended reach to reduce port/connector strain on 2-in-1 devices like Surface Pro 7, iPad Pro, HP Elite x2 & laptops on riser stands
- **PORTABLE & COMPACT:** Portable all-in-one USB Type-C multiport adapter is made from durable aluminum & designed for easy transport in a laptop bag for convenient on-the-go use between office, home office, shared office spaces, and business travel
- **RELIABLE PERFORMANCE:** USB bus powered or via external USB-C power adapter; 100W Power Delivery 3.0 pass through w/ 12W reserved for adapter to avoid video flickering, device dropouts or overdrawing power common in other hubs; up to 88W for laptop charging
- **WIDE COMPATIBILITY:** Compatible with USB-C laptops, ultrabooks & Chromebooks, plus Thunderbolt 3 laptops from HP, Dell, Lenovo, MacBooks (Intel processor & M1 chip), and Surface Laptop 4; USB-C mini dock works w/ Windows, macOS, iPadOS, Android & Chrome OS
- **4K 60HZ WITH DP 1.4 ALT-MODE:** Supports 4K 60Hz on host devices that support DP 1.4 Alt-Mode (min. Intel 11th Gen); on host devices that support DP 1.2 Alt-Mode, maximum video output resolution is 4K 30Hz; works w/ ultra-wide monitors up to 3440x1440@60Hz

---

## Hardware

Warranty	3 Years
4K Support	Yes
Fast-Charge Port(s)	No
Displays Supported	1
Interface	USB 3.2 Gen 1
Bus Type	USB-C
Industry Standards	IEEE 802.3 IEEE 802.3u IEEE 802.3ab USB 3.0 - Backward compatible with USB 2.0 and 1.1
Chipset ID	Realtek - RTL8153 Parade Technologies - PS176 VIA Tech - VL102

VIA Tech - VL817

---

**Performance**

Maximum Data Transfer Rate	5 Gbps (USB 3.0) <br / >2 Gbps (Ethernet; Full-Duplex)
Maximum Digital Resolutions	4K @ 60Hz (on hosts that support DP 1.4), 4K @ 30Hz (on hosts that support DP 1.2)
Type and Rate	USB 3.0 - 5 Gbit/s
UASP Support	Yes
Compatible Networks	10/100/1000 Mbps
Full Duplex Support	Yes

---

**Connector(s)**

Connector Type(s)	HDMI (19 pin)  RJ-45  USB Type-A (9 pin) USB 3.0 (5 Gbps)  USB-C (24 pin) USB Power Delivery only
Host Connectors	USB Type-C (24 pin) USB 3.0 (5Gbps)

---

**Software**

OS Compatibility	Windows 7, 8, 8.1, 10<br / >macOS 10.9 to 10.15, 11.0<br / >Chrome OS
------------------	-----------------------------------------------------------------------

---

**Power**

Power Source	Bus Powered and Host USB-C Power Adapter
Power Delivery	100W

---

**Environmental**

Operating Temperature	0 to +45
Storage Temperature	-10 to +70
Humidity	10% to 90 % RH

---

**Physical Characteristics**

Color	Black & Gray
-------	--------------



Material	Plastic
Cable Length	11.8 in [30 cm]
Product Length	1.8 in [45.0 mm]
Product Width	11.8 in [30.1 cm]
Product Height	0.5 in [13.0 mm]
Weight of Product	3.3 oz [93.0 g]

---

**Packaging Information**

Package Length	6.7 in [17.0 cm]
Package Width	5.6 in [14.2 cm]
Package Height	1.2 in [30.0 mm]
Shipping (Package) Weight	4.4 oz [126.0 g]

---

**What's in the Box**

Included in Package	USB-C Multiport Adapter
	Product Insert

---

*\*Product appearance and specifications are subject to change without notice.*

