

RSC24/7

Mobile roller cab with 7 drawers

New ABS reinforced worktop, designed to support tool chests RSC22, RSC23, RSC23C and RSC23T.

Main features:









- 7 fully removable drawers (588x367 mm), with ball bearing slides:
- 5 drawers, 70 mm high
- 1 drawer, 140 mm high
- 1 drawer, 210 mm high
- Multi-purpose top with anti-fall edges and eight holes for accommodating screwdrivers
- Four castors Ø 125 mm:
- 2 fixed and 2 steering (one with brake).
- Front centralized safety lock.
- Static load capacity: 800 kg.
- Built-in bottle holder (can be applied on both sides).
- The following accessories can be added:
- wood worktop 2400 RSC24/PL
- perforated tool panel 2400 RSC24/PF
- folding shelf 2400 RSC24/MP
- computer wall bracket 2400 RSC24/SPC
- document holder 2400 RSC24//PD (available in anthracite grey or black)
- paper roll holder 2400 RSC24/PC (available in anthracite grey or black)
- Drawer bases protected by foamed rubber mats.
- Each drawer can accommodate up to 4 EVA foam or ABS thermoformed trays.

 63 kg

The evolution of the C24S roller cab!

Reinforced worktop and a wide range of dedicated accessories!

Available in 7 different colour combinations!

	art.		
024004070	RSC24/7-FO		Orange
024004071	RSC24/7-O		RAL 2011 - 7016
024004072	RSC24/7-G		RAL 9006 - 7016
024004073	RSC24/7-R		RAL 3000 - 7016
024004076	RSC24/7-B		RAL 5015 - 7016
024004077	RSC24/7-A		RAL 7016
024004079	RSC24/7-N		RAL 9005

