

Han B Protect Cover Die Cast (Easy hood)



Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---|
| Part number | 11 30 024 5422 |
| Specification | Han B Protect Cover Die Cast (Easy hood) |
| HARTING eCatalogue | https://harting.com/11300245422 |

Identification

| | |
|------------------------------|--|
| Category | Accessories |
| Series of hoods/housings | Han [®] Easy Hood |
| Type of accessory | Protection cover |
| Description of the accessory | for hoods a ... d With fixing cord |

Version

| | |
|--------------|----------------------|
| Size | 24 B |
| Locking type | Double locking lever |

Technical characteristics

| | |
|--|-----------------|
| Limiting temperature | -40 ... +125 °C |
| Degree of protection acc. to IEC 60529 | IP54 |
| Type rating acc. to UL 50 / UL 50E | 4 4X 12 |

Material properties

| | |
|-------------------------|-----------|
| Material (hood/housing) | Metal |
| Material (seal) | NBR |
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | e |



Pushing Performance
Since 1945

Material properties

| | |
|--------------------------------------|---|
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Yes |
| REACH SVHC substances | Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate |
| ECHA SCIP number | 60b1a572-bb3f-476f-9307-b7d1688bd90c |
| California Proposition 65 substances | Yes |
| California Proposition 65 substances | Lead Nickel |
| Fire protection on railway vehicles | EN 45545-2 (2020-08) + A1 (2023-10) |
| Requirement set with Hazard Levels | R22 (HL 1-3) R23 (HL 1-3) |

Specifications and approvals

| | |
|-----------|--------|
| Approvals | DNV GL |
|-----------|--------|

Commercial data

| | |
|--------------------------------|--|
| Packaging size | 1 |
| Net weight | 118.433 g |
| Country of origin | Germany |
| European customs tariff number | 85389099 |
| GTIN | 5713140110847 |
| eCl@ss | 27440208 Cap for industrial connectors |
| ETIM | EC002314 |
| UNSPSC 24.0 | 39121467 |