

Chemical-resistant gloves offering superior grip and advanced dexterity

- **Specialized protection:** AlphaTec® 58-270 safety gloves possess a thin nitrile shell, which enables EN 374 Type A chemical protection with breathable comfort
- **Reinforced grip:** ANSELL GRIP™ coating ensures class-leading grip, for more secure handling
- **Enhanced features:** AlphaTec® 58-270 industrial gloves' special safety cuffs make them easy to don and remove, facilitating daily use
- **Augmented dexterity:** Their seamless 15-gauge design helps reduce strain and augment dexterity
- **Elevated comfort:** In addition, their nylon liner retains less heat, reducing perspiration and ensuring greater comfort
- **Improved durability:** These AlphaTec® gloves are hard-wearing, with ANSI/ISEA 105-2024 ABRASION LEVEL 4 and EN ABRASION LEVEL 3



Industries

- Automotive
- Automotive Aftermarket
- Machinery and Equipment
- Metal fabrication
- Chemical
- Agriculture

Applications

- Body painting including surface inspection
- Applying sealers, touching up
- Press injection molding
- Equipment repair & maintenance
- Assembling and mounting components
- Painting or cleaning tools or robots
- Final assembly
- Metalwork, glass processing
- Assembly & inspection of components
- Warehousing of raw materials
- Testing

Key Features

- **Thin, durable nitrile shell:** EN 374 Type A chemical protection
- **ANSELL GRIP™ coating:** For PPE gloves that offer superior grip
- **Generous safety cuff:** Safety gloves that are easy to put on and remove

Vulcanization Chemical Accelerators

- Zinc Diethyldithiocarbamate

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Technologies



Performance Standards

ANSI/ISEA 105-2024



0493

EN388: 2016



3121A

EN ISO 374-1:2016



JKLOPT

EN ISO 374-5



VIRUS



G2
ISO 18889



Specifications

BRAND STYLE	DESCRIPTION	SIZE	LENGT H	COLOR	PACKAGE
AlphaTec® 58-270	Liner Material: Nylon Coating Material: Nitrile Featured Technology: ANSELL GRIP™	6, 7, 8, 9, 10, 11	300 / 11.8	Grey	• 12 pairs per bag, 12 bags per case • Vend pack variant ,1 pair per bag ,72 bags per carton

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada Inc.
105, rue Lauder
Cowansville (Québec)
J2K 2K8, Canada
T: 1 800 363-8340
F: 1 888 267-3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.