

FEATURES

- Interlocked and RCD (Residual-current device) protected
- IP67 Rated
- Wall mountable
- Red and blue colours offered in this range of power connectors
- Voltage ratings of 415V and 230V offered in this range
- Angled socket, allowing a more convenient connection
- All models offered in the range are highly reliable and excellent quality
- Manufactured from self-extinguishing & shock resistant thermoplastic

RS PRO IP67 Red Wall Mount 3P+N+E RCD Industrial Power Connector Socket, Rated At 16.0A, 415.0 V

RS Stock No.: 410-034



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

From the trusted brand RS PRO, comes a range of high-quality wall mountable power connectors. Manufactured to industry standards these connectors are easy to assemble and are a fantastic industrial plug solution for powering tools and machinery at a range of different voltage requirements.

General Specifications

Commercial Series	ADVANCE 2 Series
Syntetical description	INTERLOCKED SOCKET + RCD
Hour position	6h
Pole Format	3P+N+E
Gender	Female
Body Orientation	Angled
Material	Engineering Plastic
Colour	Red
Applications	Providing power for machinery on construction sites, Woodworking machines, Maintenance workshops in the light industry

Electrical Specifications

Type of Current	AC
Current Rating	16A
Voltage Rating	415V
Working Frequency	50Hz; 60Hz
Plug/Socket	Socket
Termination Method	Pre-Wired

Mechanical Specifications

Mounting Type	Wall Mount
----------------------	------------

Protection Category

IP Rating

IP67

Approvals

Compliance/Certifications

EN61340

