

Eaton 12BDGHO20

Catalog Number: 12BDGHO20

Air fuse-link, medium voltage, 20 A, AC 12 kV, 441 x 50.8 mm, back-up, BS, with striker

General specifications



Product Name	Catalog Number
Eaton Bussmann series medium voltage BS air fuse	12BDGHO20 EAN 5027590431446
Product Length/Depth	Product Height
359 mm	50.8 mm
Product Width	Product Weight
50.8 mm	2100 g
Certifications	
CE	

Product specifications

Resources

Type

Fuse

Application

protection of primary side
transformers
used in fuse switch
combination units, fuse
bases and fuse switches

Amperage Rating

20 A

Fuse indicator

With Striker

Fuse size

51 x 359 mm

Breaking capacity

40 kA

Installation technique

Air

Performance Cat According To IEC 60282-1

Back-up

Product application

Primary side transformer protection

Rated frequency - max

50 Hz

Rated frequency - min

50 Hz

Release characteristic

Other

Standard

British Standard

Utilization category

Other

Voltage type

AC

With striker

Yes

Class

Class back-up

Fuse shape

Cylindrical, offset bolted tags

Fuse diameter

51 mm

Interrupt rating

40 kAIC

Construction size

51 x 359 mm

Mounting method

Clip-in

Voltage rating

12 kV

Fuse type

BDGH



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia