



Centurion Bulkhead Maintained / Non-Maintained 5W White



- High lumen performance LED polycarbonate bulkhead for increased spacings
- Supplied with self-adhesive legend
- Self-test as standard
- 20mm conduit entry positions and rear terminal box entry
- Hinged screwless gear tray for ease of installation
- Viewing distance 18 metres

General Information

Lamp Type	LED
Emergency	Yes
Self Test	Yes
IP Rating	IP65
IK Rating	IK08
Class Protection	1
Internal / External	Internal / External
Surface / Recessed / Suspended	Surface
Warranty (Years)	5





Material	Polycarbonate
Technical Information	
Wattage	5W
Lumens Delivered	160lm (Emergency)
Beam Angle	110
CRI	70
CCT	6500K
Input	220/240V
Hertz	50/60Hz
Operating Temp	0°C to 40°C
Lumen Depreciation	L70 50,000h
Power Factor	0.38

