

# Reducing nipple NPFC-RS-G12-G38-MF

Part number: 8142598

FESTO



 [General operating condition](#)

## Data sheet

| Feature                                           | Value                                     |
|---------------------------------------------------|-------------------------------------------|
| Material threaded fitting                         | Nickel-plated brass                       |
| Size of pack                                      | 10                                        |
| Operating pressure                                | -0.95 bar ... 10 bar                      |
| Operating medium                                  | Compressed air to ISO 8573-1:2010 [-:~:-] |
| Corrosion resistance class CRC                    | 1 - Low corrosion stress                  |
| LABS (PWIS) conformity                            | VDMA24364-B2-L                            |
| Ambient temperature                               | -10 °C ... 60 °C                          |
| Nominal tightening torque, pneumatic connection 1 | 47.9 Nm                                   |
| Tolerance for nominal tightening torque           | ± 20%                                     |
| Product weight                                    | 22.84 g                                   |
| Pneumatic connection, port 1                      | G1/2                                      |
| Pneumatic connection, port 2                      | G3/8                                      |
| Note on materials                                 | RoHS-compliant                            |
| Material seals                                    | PVC                                       |