

FR50 - Bizflame Work FR Coverall

Collection: Bizflame™ Work

Range: Flame Resistant Multi-Norm

Shell Fabric: Bizflame Work: 99% Cotton, 1% Carbon Fibre 350g

Product information

This coverall is perfect for the demands of the offshore industry. Constructed with a highly innovative flame-retardant fabric with high visibility reflective tape double stitched for enhanced visibility. Meeting all the required EN standards, features include triple stitched seams, high visibility strips on shoulders, arms and legs, concealed 2-way front brass zip and two front slant chest pockets with concealed brass zips.

Standards

EN ISO 11612 (A1+A2, B1, C1, E2, F1)

EN ISO 11611 Class 2 (A1+A2)

EN 1149 -5

IEC 61482-2 IEC 61482-1-1 (ELIM 8.6 CAL/CM², ATPV 9.8 CAL/CM²)

IEC 61482-2 IEC 61482-1-2 APC 1

EN 17353 Type B2

ASTM F1959/F1959M-12 (ATPV=13.6 Cal/CM² (HAF=82%))

Bizflame™ Work

BizFlame™ Work has been developed and designed using a highly innovative flame-resistant fabric with added anti-static properties. This material is constructed from 99% Cotton and interwoven with 1% Carbon Fibre. Its excellent tear and tensile strength offer durability, while the premium quality Cotton provides unrivalled comfort. The anti-static property is inherent due to the Carbon content.

Flame Resistant Multi-Norm

This industry leading flame resistant range provides multi-standard protection for hazardous environments. These state of the art products are the result of years of experience combined with advanced technology and market research. Commitment to the health, safety and comfort of the wearer can be seen in the wide range of products suitable for all climates and end uses.

Features

- Protection against radiant, convective and contact heat
- Class 2 welding protection
- Rule pocket
- Two back patch pockets
- Hook and loop cuffs for a secure fit
- Action back for extra freedom of movement



FR50 - Bizflame Work FR Coverall
Commodity Code: 6211321000

Test House

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)
 Bracetown Business Park
 D15 YN2P, Ireland
 Cert No: 2777/13136-03/E00-00

OETI (Institut fuer Oekologie, Technik und Innovation GmbH) (Notified Body No.: 0534)
 Sebenhirtenstrasse 12A
 1230, Austria
 Contact: Marion Pfeiler
 Cert No: 0598

Wash Care



Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	GTIN/DUN14
FR50GRRXS	Grey	43.0	28.0	50.0	1.5000	0.0602	5036108305018	25036108794045
FR50GRRS	Grey	43.0	28.0	50.0	1.5200	0.0602	5036108284108	25036108774290
FR50GRRM	Grey	43.0	28.0	50.0	1.6000	0.0602	5036108284092	25036108774283
FR50GRRL	Grey	43.0	28.0	50.0	1.7000	0.0602	5036108284085	25036108774276
FR50GRRXL	Grey	43.0	28.0	50.0	1.6600	0.0602	5036108284115	25036108774306
FR50GRRXXL	Grey	43.0	28.0	55.0	1.7400	0.0662	5036108284122	25036108774313
FR50GRRXXXL	Grey	43.0	28.0	55.0	1.8700	0.0662	5036108305025	25036108794052
FR50GRR4XL	Grey	43.0	28.0	55.0	1.9200	0.0662	5036108304998	25036108794021
FR50GRR5XL	Grey	43.0	28.0	55.0	1.9700	0.0662	5036108305001	25036108794038