

FEATURES

- Quick and easy installation
- Powerful flashing signal light
- Snap fit mounting plate design
- Ideal for use both indoors and outdoors

RS PRO Blue Xenon Beacon, 10 → 100 V dc, Flashing, Surface Mount

RS Stock No.: 236-385



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This Xenon Beacon from our own RS PRO brand is high quality flashing beacon ideal for use in wide range of applications requiring a low cost and energy efficient signalling solution. The snap fit design of the mounting plates allows you to install the xenon beacons with ease, with one plate being attached to the beacon and the other to the surface. This range of flashing beacons from RS PRO are suitable for light and heavy industrial signalling applications, producing a powerful flashing light source to signal hazards and emergencies. It is supplied with lens and bulb.

General Specifications

Nominal flash rate	75 per minute
Bulb Type	Xenon
Light Effect	Flashing
Lens Colour	Blue
Magnetic type	No
Housing Colour	Black
Lamp Include	Yes
Multifunction	No
Number of LED	1
Special Features	Low Profile & Compact Design

Electrical Specifications

Supply Voltage	10VDC to 100VDC
Current Type	DC
Current Consumption	100 mA, 130 mA, 215 mA, 395 mA, 460 mA

Mechanical Specifications

Dimensions	130mm (h)
Base Diameter	150mm
Mounting Style	Surface Mount

Operation Environment Specifications

Maximum Temperature	-30°C
Minimum Temperature	+50°C

Protection Category

IP Rating	IP 56
------------------	-------

Approvals

Standards Met	EMC (ECE R10), RoHS Compliant
----------------------	-------------------------------

