



基板取付穴推奨寸法

(基板厚: t=1~1.6mm)
RECOMMENDED PC BOARD HOLE DIMENSION
(THICKNESS: t=1~1.6mm)

注記
NOTE

△ 適合ターミナル: 50034-8*00
APPLICABLE TERMINAL: 50034-8*00

| | | | |
|----|------|------------|------------------|
| 28 | 30.4 | 51015-1500 | 15 |
| 26 | 28.4 | ↑ -1400 | 14 |
| 24 | 26.4 | -1300 | 13 |
| 22 | 24.4 | -1200 | 12 |
| 20 | 22.4 | -1100 | 11 |
| 18 | 20.4 | -1000 | 10 |
| 16 | 18.4 | -0900 | 9 |
| 14 | 16.4 | -0800 | 8 |
| 12 | 14.4 | -0700 | 7 |
| 10 | 12.4 | -0600 | 6 |
| 8 | 10.4 | -0500 | 5 |
| 6 | 8.4 | -0400 | 4 |
| 4 | 6.4 | ↓ -0300 | 3 |
| 2 | 4.4 | 51015-0200 | 2 |
| B | A | ENG.NO. | 種数 NO. OF CKT |

| | | | | | |
|-------------------------|-------|-------------|----------------------|-----------|-----------|
| 角度 ANGLE | ±3° | | | | |
| 30以上 OVER | +0.3 | | | | |
| 10以上 30未満 UNDER | +0.25 | | | | |
| 10未満 UNDER | +0.2 | | | | |
| 一般公差 GENERAL TOLERANCES | | 記号 LTR | 変更内容 REVISION RECORD | DR. CHK. | 日付 DATE |
| | B | 再作図 REDRAWN | LC703101 | H.J. M.F. | '96/05/20 |
| | | | | | |
| | | | | | |
| | | | | | |
| | | | | | |
| | | | | | |
| | | | | | |
| | | | | | |
| | | | | | |
| | | | | | |

材料 MATERIAL
ナイロン66, UL94V-0
NYLON66, UL94V-0

仕上げ FINISH —

適用電線範囲 WIRE RANGE —

被覆外径 INS. RANGE —

DRAWN BY '96/05/28 H.I.IJIMA
CHK'D BY '96/05/28 M.FUKUSHIMA

APP'D BY '96/05/28 M.ENOMOTO

尺度 SCALE 8 : 1

molex MOLEX-JAPAN CO.,LTD.
日本モレックス株式会社

REVISE ONLY ON CAD SYSTEM

TITLE 名称
2.0 BOARD
IN CONN. HSG.

DWG. NO. SD-51015-**-00

REV B