

**Datasheet**

**300 W Straight Immersion Tank Heater, Thermostat Included, 220 → 240 V ac**

RS Stock number 790-4823



**Explosion proof Aquarium heaters Heating Elements**

Item No.	AH-100
Voltage	AC220-240V
Frenquency	50~60Hz
Power	100W
Precision	(20°C~34°C) ±0.5°C
Water Capacity	120L(32 Gallons)
Size	Dia2.2cm*L25m

**DESCRIPTION**

Aquarium heaters are used for heating water in domestic fish tanks and industrial small water tanks to maintain temperatures between 20-34deg C.

They are available in three different wattages as above.

**CONSTRUCTION**

The heaters are made from explosion proof glass for added protection and are

supplied with suction cups for fitting. A finger adjustable thermostat is fitted for temperature setting.

**INSTALLATION**

The heaters should always be fitted below the waterline for best use and premature failure. Suction cups to be used on a smooth surface.

Item No.	AH-200
Voltage	AC220-240V
Frenquency	50~60Hz
Power	200W
Precision	(20°C~34°C) ±0.5°C
Water Capacity	200L(53 Gallons)
Size	Dia2.2cm*L30cm

Item No.	AH-300
Voltage	AC220-240V
Frenquency	50~60Hz
Power	300W
Precision	(20°C~34°C) ±0.5°C
Water Capacity	375L(99 Gallons)
Size	Dia2.2cm*L35cm