

Hydraulic hand crimping tool and connectable hydraulic compression heads for terminals

Hydraulic hand crimping tool 10 to 70 mm²

- Hand crimping tool.
 - Power: 55 kN.
 - Crimping from 10 to 70 mm².
 - Two pressure level.
 - Automatic release.
 - Die lock system.
 - Head tilting on 180°.
- Delivered in box with working leaflet.

Ref.	SNCF
TR1461	7-847-7296



Connectable hydraulic compression head 10 to 95 mm²

- Connectable hydraulic compression head.
- Power: 100 kN.
- Crimping from 10 to 95 mm².
- anti-corrosion coating (nickel).
- Die locking system.
- To be connected to 700 bars hydraulic pump or sets.
- Delivered with female semi-coupler p/n: RKFM38NPT.

Ref.
TR1462



Crimping dies:

Dies	Cross section (mm ²)	Terminals series	Ref.	SNCF code
	10	pre-insulated ELP series	ELP460	7.847.7303
	16	pre-insulated FLP series	FLP460	7.847.7304
	25	pre-insulated NP series	NP460	7.847.7305
	10	non insulated ELS series	ELS460	7.847.7297
	16	non insulated FLS series	FLS460	7.847.7298
	25	non insulated TN 25 series	TN25-460	7.847.7299
	35	non insulated TN35 series	TN35-460	7.847.7300
	50	non insulated TN 50 series	TN50-460	7.847.7301
	70	non insulated TN70 series	TN70-460	7.847.7302
	95*	non insulated TN95 series	TN95-460	

*only with TR1462 tool.