

## Datasheet

# RS Pro Straight 50Ω Panel Mount TNC Connector, jack, Crimp Termination

RS Stock No: **793-3617**



## Product Details

RS Pro panel mount TNC connector jack is designed for 50 Ω impedance applications. This straight connector jack offers crimp termination. The waterproof, coaxial clamp jack comes with complete IP68 sealing against gas and moisture ingress along the whole connector. This bulkhead clamp jack has a nickel plated brass body, PTFE insulator, silicone 'O' rings and a gold plated centre contact. It is suitable for use with RG-174/U cables.

## Features and Benefits

- Nominal impedance 50Ω
- Gold-plated contacts
- Crimp termination

**Specifications:**

Body Orientation	Straight
Body Plating	Nickel
Contact Material	Gold
Contact Plating	Brass
Gender	Female
Impedance	50 $\Omega$
Mounting Type	Panel Mount
Operating Frequency	0 to 3 GHz
Termination Method	Crimp
Dimensions	27.6 x 7.16 mm
Operating Temperature Range	-65 to +165°C