



Fuse-link, low voltage, 800 A, AC 440 V, 120 kA, NH3, gL/gG, IEC, dual indicator, live gripping lugs

Part no. NH FUSE 800A 440V GG/GL SIZE 3
Catalog No. 800NHG3B

EL-Nummer (Norway) 1664089

Delivery program

| | | | |
|------------------------------|---|----|--|
| Product range | | | Fuse |
| Basic function | | | Fuse-link |
| Field of application | | | low voltage |
| Rated current | I | A | 800 |
| Rated voltage | | | AC 440 V |
| Construction size | | | NH3 |
| Utilization category | | | gL/gG |
| Status indicator | | | dual indicator |
| Description | | | live gripping lugs |
| Breaking Capacity | | kA | 120 |
| usable for size/applications | | | industrial |
| Standard/Approval | | | IEC |
| Shape | | | square body with knife blade contacts |
| Standards/Regulations | | | IEC 60269-2 fuse system A DIN 43620 VDE 0636-2 |

Technical data ETIM 7.0

| | | | |
|---|--|----|---|
| Circuit breakers and fuses (EG000020) / Low Voltage HRC fuse (EC000055) | | | |
| Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Low-Voltage HRC fuse (ecl@ss10.0.1-27-14-20-05 [AFZ800015]) | | | |
| Construction size | | | NH3 |
| Rated current | | A | 800 |
| Rated voltage | | V | 440 |
| Voltage type | | | AC |
| Rated switching capacity | | kA | 120 |
| Utilization category | | | gL/gG (cable protection/equipment protection) |
| Type of fuse status indicator | | | Combination fuse status indicator |
| Insulated metal gripping lugs (IMGL) | | | No |